

DETECTAMET

Technical Data Sheet

Document Reference	535
Date of Issue	16 th Feb 2026
Revision Number	001
Date of Last Revision	16 th Feb 2026

535 Stackable Pouring Jug



Technical Data Sheet Applicable To:

535-S012-T100-P0*	Detectable Stackable Pouring Jug 1000ml (33.81 fl oz)(All colours)
535-S018-T100-P0*	Detectable Stackable Pouring Jug 2000ml (67.62 fl oz)(All colours)

Industry Usage:

This stackable pouring jug comes in two sizes and nine different colours and is manufactured from EU and FDA food contact approved detectable polymer.

Features and Benefits:

- Metal detectable & X-ray visible
- Manufactured from EU & FDA food contact approved detectable polymer
- Metric/imperial measurements inside
- Stackable

- Small 1000ml (33.81 fl oz) height 120mm (4.72") dia 115mm (4.52")
- Large 2000ml (67.62 fl oz) height 157mm (6.18") dia 145 (5.70")

Material and Compliance information:

All above products are both Metal Detectable & X-ray visible.

The above is manufactured using pigments which are in accordance with: -

- European Resolution AP (89) 1
- Recommendation IX of the BfR for colouring plastics
- EN71-3 Toy regulation
- EU regulation EU No 2019/1381 amending Regulation EU No 1935/2004
- Is based on a polymer carrier that is compliant with: -
- EU regulation EU No 2020/1245 amending and correcting Regulation (EU) No 10/2011
- EU regulation EU No 2019/1381 amending Regulation EU No 1935/2004
- Has been produced according to Regulation 2023/2006/EC on good manufacturing practice for materials and articles intended to come into contact with food, applicable to plastic raw materials.

This compliance statement is based on information supplied by the polymer and pigment manufacturers, migration testing according to Regulation 10/2011, migration modelling and quality control systems in place at Detectamet.

REACH – No substances of very high concern (SVHC) above the 0.1% weight (w/w) threshold limit are present in the materials.

These products above are free from PFAS (per- and polyfluoroalkyl) and Phthalates

These products do not contain any Bisphenol A, S or F or any other substances suspected of being endocrine disruptors.

Regulations and Standards

We confirm that the above-mentioned products are suitable for use in contact with all food types and are in conformity with the applicable requirements of the following regulations and standards:

- Regulation (EC) no. 1935/2004 on Materials and Articles intended to come into contact with food.
- Commission Regulation (EU) No 10/2011 on Plastic materials intended to come into contact with food including all its updates.
- Regulation (EC) No. 2023/2006 on Good Manufacturing Practice for materials and articles intended to come into contact with food.
- Council of Europe Resolution AP 89/1 on the use of Colorants in Plastic Materials coming into contact with food.
- Council of Europe Resolution AP 89/1 on the use of Colorants in Plastic Materials coming into contact with food.
- US FDA 21 CFR 177.1520 (Olefin polymers) with colorants and additives cleared for use through listing in 178.3297 (Colorants for polymers), 178/2010 (antioxidants and/or stabilisers for polymers, or other respective parts of the FDA regulations)

Migration test data obtained under short term-repeat use test condition (6dm²/kg food) has demonstrated that levels of overall migration and specific migration of additives from these products will not exceed the legal limits with all food types.

Test Simulants	Food Types	Testing Condition
A-C, D1, D2 of Regulation No. 10/2011 for Plastic Materials and Articles in contact with food.	All dry, aqueous, acidic, alcoholic and fatty foods	2 hours at 70c, Repeat use. Test OM3 of regulation 10/2011

Dual-use food additives may be present but any migration into food will be minimal. This compliance statement is based on information supplied by the polymer and pigment manufacturers, migration testing according to Regulation 10/2011, migration modelling and quality control systems in place at Detectamet.

General Information:

Maximum Use Temperature: 100c

Maximum wash Temperature: 121c

Maximum use Temperature: Do not store at deep freeze temperatures prior to use.

Cleaning:

It is recommended that prior to and after use, scrapers are cleaned, disinfected & sterilized, as appropriate to their intended use (to minimise risk of microbial Growth and cross contamination, maximising their efficiency and durability).

REACH – No substances of very high concern (SVHC) above the 0.1% weight (w/w) threshold limit are present in the materials.

No warranty is given or implied with respect to this information or patent infringement. Detectamet Ltd do not accept liability for loss or damage arising from the use of this information. Results are based on a test sample, our general experience and information from suppliers. Data and results may be confirmed by the buyer by testing for its intended conditions of use.

Safety You Detect

detectamet.global

